

Case History no. 21 – Solvent Filtration in Pharmaceutical Industry Using Mobile Filter Rig

Fluid	: Various Solvents
Flow	: 10m ³ /hr
Pressure	: 4 barg
Temperature	: 0 – 80 °C

Problem:-

A client in the pharmaceutical industry was looking for a mobile portable filter system to filter solvents and parental solutions at various locations in their facility.

Solution: -

We sold them an Ronningen-Petter mobile porta-basket filter in 316L stainless steel on a 316 stainless steel mobile rig complete with anti-static, non-marking wheels, Teflon seals and polypropylene filter bag. Elbowed outlet.

Result:-

They have since purchased a further 7 to 8 units.